

Garant
**Clamping toolholder MWLNL 95°, for indexable inserts WN., left-hand,
Shank / insert size: 32/08mm**

Order data

Order number	251913 32/08
GTIN	4045197656964
Item class	21T

Technical description

Screw set	259023 2
Insert size	8 mm
Shim	259031 41
Shank size	32 mm
Clamping claw	259038 12
Pin	259049 2
Head length L ₁	32 mm
Functional width L ₄	40 mm
ISO code toolholder	MWLNR/L 3232P08
suitable indexable insert	WN.. 0804..
Overall length L	170 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	95 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of screws 10 pieces Type 2	259023 2
Shim Type 41	259031 41
Clamping claw Type 12	259038 12
Pin Type 2	259049 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3