

**Garant**

**Carbide boring bar E.. SDQCR 107,5°, for indexable inserts DC., right-hand,  
Shank Ø / insert size: 8/07mm**

**Order data**

Order number	260320 8/07
GTIN	4067263622376
Item class	21T

**Technical description**

Shank Ø D <sub>s</sub>	8 mm
Insert size	7 mm
Overall length L	125 mm
Clamping height L <sub>2</sub>	7.6 mm
Overhang L <sub>1</sub>	29 mm
Centre offset L <sub>3</sub>	7 mm
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Setting angle κ	107.5 degrees
Minimum pre-drill Ø D <sub>min</sub>	12 mm
ISO code toolholder	E08K SDQCR/L07
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8