

**Garant**
**Clamping toolholder SDHCR 107,5°, for indexable inserts DC., right-hand,  
Shank / insert size: 10/07mm**

**Order data**

Order number	260306 10/07
GTIN	4045197654861
Item class	21T

**Technical description**

Functional width $L_4$	12 mm
Head length $L_1$	7 mm
Pack of insert screws	269028 22
Shank size	10 mm
Insert size	7 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	SDHCR/L 1010E07
Overall length L	70 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle $\kappa$	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15