

Garant
Clamping toolholder PSSNL 45°, for indexable inserts SN., left-hand, Shank / insert size: 25/15mm

Order data

| | |
|--------------|---------------|
| Order number | 251113 25/15 |
| GTIN | 4045197656797 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-----------------|
| Head length L ₁ | 35 mm |
| Lever | 259015 12 |
| Shank size | 25 mm |
| Insert size | 15 mm |
| ISO code toolholder | PSSNR/L 2525M15 |
| Shim pins pack | 259044 6 |
| suitable indexable insert | SN.. 1506.. |
| Shim punches pack | 259047 4 |
| Shim | 259031 37 |
| Functional width L ₄ | 32 mm |
| Lever screw | 259018 11 |
| Overall length L | 150 mm |
| Standard | DIN ISO 5610 |
| Application type | left-hand |
| Through-coolant | no |

| | |
|------------------------|-------------------------------|
| Setting angle κ | 45 degrees |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| Lever Type 12 | 259015 12 |
| Lever screw Type 11 | 259018 11 |
| Shim Type 37 | 259031 37 |
| Set of shim pins 10 pieces Type 6 | 259044 6 |
| Shim punches set 10 pieces Type 4 | 259047 4 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| Precision Bit for Torx®, 1/4 inch E 6.3 Torx® profile TX15 | 674248 TX15 |