

Garant
Clamping toolholder PSKNL 75°, for indexable inserts SN., left-hand, Shank / insert size: 32/15mm

Order data

Order number	251111 32/15
GTIN	4045197650832
Item class	21T

Technical description

Insert size	15 mm
Head length L ₁	30 mm
Lever screw	259018 11
suitable indexable insert	SN.. 1506..
Shim	259031 37
Shim punches pack	259047 4
Lever	259015 12
Functional width L ₄	40 mm
ISO code toolholder	PSKNR/L 3232P15
Shank size	32 mm
Shim pins pack	259044 6
Overall length L	170 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 37	259031 37
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15