

Garant
Clamping toolholder DCLNL 95°, for indexable inserts CN., left-hand, Shank / insert size: 20/12mm

Order data

Order number	250039 20/12
GTIN	4067263121190
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holder No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Series	Master Eco
ISO code toolholder	DCLNR/L 2020K12
Overall length L	125 mm
suitable indexable insert	CN.. 1204..
Shim screw	259027 8
Insert size	12 mm
Functional width L ₄	29.5 mm
Head length L ₁	30 mm
Shim	259031 49
Shank size	20 mm

Clamp, screw, O-ring	259036 22
Standard	Works standard
Application type	left-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder

Accessories

Shim screw Type 8	259027 8
Shim Type 49	259031 49
Clamp unit Type 22	259036 22