

**Garant**
**Clamping toolholder SDJCR 93°, for indexable inserts DC., right-hand,  
Shank / insert size: 10/07mm**

**Order data**

Order number	260308 10/07
GTIN	4045197655325
Item class	21T

**Technical description**

ISO code toolholder	SDJCR/L 1010E07
Head length $L_1$	13 mm
suitable indexable insert	DC.. 0702..
Functional width $L_4$	12 mm
Pack of insert screws	269028 22
Shank size	10 mm
Insert size	7 mm
Overall length L	70 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle $\kappa$	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

**Accessories**

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15