

Garant
Carbide boring bar E.. SDUCL, for indexable inserts DC., left-hand

Order data

Order number	260325
GTIN	4045197652775
Item class	29W

Technical description

ISO code toolholder	E10K SDUCR/L07
ISO code toolholder	E12M SDUCR/L07
suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 7
Centre offset L ₃	7 mm
Centre offset L ₃	9 mm
Clamping height L ₂	9.6 mm
Clamping height L ₂	11.6 mm
Minimum pre-drill $\varnothing D_{\min}$	12 mm
Minimum pre-drill $\varnothing D_{\min}$	15 mm
Overall length L	125 mm
Overall length L	150 mm
Standard	DIN 8024
Standard	Works standard

Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes
Type of product	Boring bar

Accessories

Boring bar carbide Shank Ø / insert size 10/07 mm	260319 10/07
Boring bar carbide Shank Ø / insert size 12/07 mm	260319 12/07
Set of insert screws Type 7	269028 7