

Garant

Carbide boring bar E.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 8/07mm


Order data

Order number	260319 8/07
GTIN	4045197652706
Item class	21T

Technical description

Pack of insert screws	269028 7
Insert size	7 mm
Centre offset L ₃	7.5 mm
ISO code toolholder	E08K SDUCR/L07
Minimum pre-drill Ø D _{min}	12.5 mm
suitable indexable insert	DC.. 0702..
Overall length L	125 mm
Clamping height L ₂	7.6 mm
Setting angle κ	93 degrees
Shank Ø D _s	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8