

Garant
Clamping toolholder SCLCR 95°, for indexable inserts SC., right-hand, Shank / insert size: 20/09mm

Order data

Order number	260026 20/09
GTIN	4067263122388
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco toolholders No. 319006 – 311936 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Functional width L ₄	25 mm
Insert size	9 mm
ISO code toolholder	SCLCR/L 2020X09
suitable indexable insert	CC.. 09T3..
Shank size	20 mm
Pack of insert screws	269028 28
Overall length L	90 mm
Series	Master Eco
Head length L ₁	30 mm

Standard	Works standard
Application type	right-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder