

Garant
**Eco clamping toolholder SVJC 93°, for indexable inserts SV.., left-hand,
Shank / insert size: 20/16mm**

Order data

| | |
|--------------|---------------|
| Order number | 261137 20/16 |
| GTIN | 4067263122654 |
| Item class | 21U |

Description
Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

| | |
|---------------------------------|-----------------|
| Functional width L ₄ | 25 mm |
| suitable indexable insert | VC.. 1604.. |
| Shank size | 20 mm |
| Shim | 259033 5 |
| Pack of insert screws | 269023 3 |
| Series | Master Eco |
| Overall length L | 100 mm |
| Insert size | 16 mm |
| Shim screw | 269013 7 |
| ISO code toolholder | SVJCR/L 2020H16 |

| | |
|------------------------|-------------------------------|
| Head length L_1 | 40 mm |
| Standard | Works standard |
| Application type | left-hand |
| Through-coolant | yes |
| Setting angle κ | 93 degrees |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Screw-on toolholder |