

Garant

**Clamping toolholder MTJNR 93°, for indexable inserts TN., right-hand,
Shank / insert size: 25/16mm**



Order data

Order number	251406 25/16
GTIN	4045197650900
Item class	21T

Technical description

Shank size	25 mm
Head length L ₁	36 mm
suitable indexable insert	TN.. 1604..
Pin	259049 6
Insert size	16 mm
Clamping claw	259038 14
ISO code toolholder	MTJNR/L 2525M16
Screw set	259023 2
Functional width L ₄	32 mm
Shim	259031 32
Overall length L	150 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of screws 10 pieces Type 2	259023 2
Shim Type 32	259031 32
Clamping claw Type 14	259038 14
Pin Type 6	259049 6
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3