

Garant
Clamping toolholder MTJNL 93°, for indexable inserts TN., left-hand, Shank / insert size: 20/16mm

Order data

Order number	251407 20/16
GTIN	4045197650924
Item class	21T

Technical description

Clamping claw	259038 14
Screw set	259023 2
Pin	259049 6
Insert size	16 mm
Functional width L ₄	25 mm
Shank size	20 mm
suitable indexable insert	TN.. 1604..
ISO code toolholder	MTJNR/L 2020K16
Shim	259031 32
Head length L ₁	31 mm
Overall length L	125 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of screws 10 pieces Type 2	259023 2
Shim Type 32	259031 32
Clamping claw Type 14	259038 14
Pin Type 6	259049 6
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3