



Clamping toolholder SCLCL 95°, for indexable inserts SC., left-hand, Shank / insert size: 25/09mm



Order data

Order number	260049 25/09
GTIN	4067263109655
Item class	22E

Description

Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

Technical description

Functional width L ₄	32 mm
Insert size	9 mm
Pack of insert screws	269028 2
Standard	Works standard
suitable indexable insert	CC.. 09T3..
ISO code toolholder	SCLCR/L 2525M09
Overall length L	150 mm
Shank size	25 mm
Head length L ₁	19 mm
Application type	left-hand
Through-coolant	yes

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 2	269028 2
Torque screwdriver Type TX15	659950 TX15