

Garant
Shrink-fit chuck with cooling channel slots, SK 40 A = 130, Clamping $\varnothing D_1$: 3mm

Order data

Order number	302364 3
GTIN	4067263014317
Item class	31A

Description
Version:

- **High-temperature steel.**
- **With 4 cooling channel slots on the clamping hole.**
- **All shanks hard turned (for smooth running!).**
- **With RFID/Balluffchip bore.**

Advantage:

Improved cooling directly on the tool shank. **Facilitates the removal of small tool diameters.**

Application:

For holding end mills and drills with parallel shank to h6 tolerance. Suitable for inductive, contact and hot air shrink-fitting units.

Optional extras:

Pull studs (PS) No. 308600 – 308800, PS wrenches No. 308820 – 308835.

Technical description

Clamping $\varnothing D_1$	3 mm
$\varnothing D_2$	12 mm
Overhang dimension A	130 mm
External $\varnothing D$	17 mm
Adapter	SK 40 A = 130

Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Machining strategy	HPC
Balluffchip bore	yes
Cooling channel bore	yes
Type of product	Hydraulic chuck