



**for indexable inserts SD.. SDJCR 93°, right-hand, Shank / insert size: 25/11mm**



## Order data

Order number	260304 25/11
GTIN	4067263109679
Item class	22E

## Description

### Version:

Targeted cooling on the cutting edge.

### Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

## Technical description

Head length $L_1$	21.5 mm
Insert size	11 mm
Standard	Works standard
Shank size	25 mm
Functional width $L_4$	32 mm
Pack of insert screws	269028 2
suitable indexable insert	DC.. 11T3..
ISO code toolholder	SDJCR/L 2525M11
Overall length $L$	150 mm
Application type	right-hand
Through-coolant	yes
Setting angle $\kappa$	93 degrees

Application	External longitudinal turning
Application	Facing
Type of product	Screw-on toolholder

---

## Accessories

Set of insert screws Type 2	269028 2
Torque screwdriver Type TX15	659950 TX15