

Garant

Clamping toolholder MVJNL 93°, for indexable inserts VN.., left-hand, Shank / insert size: 20/16mm



Order data

Order number	251707 20/16
GTIN	4045197651037
Item class	21T

Technical description

Functional width L ₄	25 mm
ISO code toolholder	MVJNR/L 2020K16
Shim screw	259025 3
Screw for clamping claw	259021 1
suitable indexable insert	VN.. 1604..
Shank size	20 mm
Insert size	16 mm
Clamping claw	259038 2
Head length L ₁	32 mm
Shim	259031 39
Overall length L	125 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Screw for clamping claw Type 1	259021 1
Shim screw Type 3	259025 3
Shim Type 39	259031 39
Clamping claw Type 2	259038 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8