

# Torque screwdriver, fixed setting, set torque: 5,7N·m



## **Order data**

Order number	211750 5,7
GTIN	4045197553232
Item class	21B

# **Description**

#### **Version:**

Torque screwdriver with easy-grip 2-component T-handle. The torque is fixed. Toolholder with permanent magnet.

#### **Function:**

When the torque is reached the screwdriver triggers with clearly audible and perceptible signal. The long-travel indication gives the user an unmistakable signal that the set torque has been reached.

#### **Application:**

In conjunction with **1/4 inch bits** with **C 6.3** or **E 6.3 shank,** e.g. **Torx Plus® bit** No. **674252.** Ideal for precise tightening of indexable inserts to the specified torque.

### **Standard:**

Geprüft nach DIN EN ISO 6789.

#### Note:

#### Supplied **without** bit.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Direction of tightening: Right-hand tightening

Torque measuring accuracy: ±10 %

Bit socket: D 6,3 Bit socket: F 6.3 Torque measuring accuracy: ±10 %

Overall length L: 107 mm Blade length: 50 mm set torque: 5.7 N·m

# **Technical description**

Blade length	50 mm
Torque measuring accuracy	±10 %
set torque	5.7 N·m
Bit socket	D 6,3
Bit socket	F 6.3
Standard	DIN EN ISO 6789
Measurement process	Torque
Feedback	triggering
Connection format	Bit holder 1/4 inch
Adjustable trigger value	non-adjustable
Trigger principle	Mechanical long travel release
Overall length L	107 mm
Reversible reading	Nm
Setting the trigger value	preset
Direction of tightening	Right-hand tightening
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk
Type of product	Torque screwdriver

## **Accessories**

"TQ-Station" – storage station for torque screwdrivers 659964