

Garant
Clamping toolholder DCLNL 95°, for indexable inserts CN., left-hand, Shank / insert size: 20/12mm

Order data

Order number	250017 20/12
GTIN	4045197649898
Item class	21T

Technical description

Insert size	12 mm
Clamp, screw, spring	259035 2
Shim screw	259025 10
ISO code toolholder	DCLNR/L 2020K12
Shank size	20 mm
suitable indexable insert	CN.. 1204..
Functional width L ₄	25 mm
Head length L ₁	30 mm
Shim	259031 2
Overall length L	125 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim screw Type 10	259025 10
Shim Type 2	259031 2
Clamp unit Type 2	259035 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20