

Garant

Steel boring bar A.. PCLNL 95°, for indexable inserts CN., left-hand, Shank Ø / insert size: 20/09mm


Order data

Order number	250037 20/09
GTIN	4045197650221
Item class	21T

Technical description

Lever screw	259018 9
Centre offset L_3	13 mm
ISO code toolholder	A20Q PCLNR/L09
Minimum pre-drill $\varnothing D_{min}$	25 mm
Insert size	9 mm
suitable indexable insert	CN.. 09T3..
Lever	259015 11
Overall length L	180 mm
Clamping height L_2	18 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Lever Type 11	259015 11
Lever screw Type 10	259018 10
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2