

**Garant**
**Clamping toolholder MWLNR 95°, for indexable inserts WN., right-hand,  
Shank / insert size: 20/08mm**

**Order data**

Order number	251912 20/08
GTIN	4045197651259
Item class	21T

**Technical description**

ISO code toolholder	MWLNR/L 2020K08
Pin	259049 2
Shim	259031 41
Insert size	8 mm
Screw set	259023 2
Functional width L <sub>4</sub>	25 mm
Clamping claw	259038 12
Head length L <sub>1</sub>	28 mm
suitable indexable insert	WN.. 0804..
Shank size	20 mm
Overall length L	125 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of screws 10 pieces Type 2	259023 2
Shim Type 41	259031 41
Clamping claw Type 12	259038 12
Pin Type 2	259049 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3