

Garant
Clamping toolholder PCLNL 95°, for indexable inserts CN., left-hand, Shank / insert size: 25/16mm

Order data

Order number	250019 25/16
GTIN	4045197654359
Item class	21T

Technical description

Head length L ₁	33 mm
ISO code toolholder	PCLNR/L 2525M16
Shim pins pack	259044 6
Lever	259015 12
Shank size	25 mm
Shim	259031 35
Lever screw	259018 11
suitable indexable insert	CN.. 1606..
Functional width L ₄	32 mm
Insert size	16 mm
Shim punches pack	259047 4
Overall length L	150 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4