

Garant

Clamping toolholder SCLCR 95°, for indexable inserts CC., right-hand, Shank / insert size: 10/06mm



Order data

Order number	260006 10/06
GTIN	4045197651600
Item class	21T

Technical description

Shank size	10 mm
ISO code toolholder	SCLCR/L 1010E06
Head length L ₁	10 mm
Insert size	6 mm
Functional width L ₄	12 mm
Pack of insert screws	269028 22
suitable indexable insert	CC.. 0602..
Overall length L	70 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22

269028 22