

Garant
**Clamping toolholder CKJNR 93°, for indexable inserts KNUX., right-hand,
Shank / insert size: 32/16mm**

Order data

Order number	251008 32/16
GTIN	4045197654632
Item class	21T

Technical description

Shim pins pack	259044 3
Insert size	16 mm
Shim	259031 4
Shank size	32 mm
Functional width L ₄	40 mm
Clamp	259038 16
Screw for clamp	259021 3
suitable indexable insert	KNUX 1604.. R/L
Head length L ₁	32 mm
ISO code toolholder	CKJNR/L 3232P16
Spring	259046 3
Overall length L	170 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Screw for clamping claw Type 3	259021 3
Shim Type 4	259031 4
Clamping claw Type 16	259038 16
Set of shim pins 10 pieces Type 3	259044 3
Spring Type 3	259046 3
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4