

Garant

**Clamping toolholder MWLNR 95°, for indexable inserts WN., right-hand,
Shank / insert size: 32/08mm**



Order data

| | |
|--------------|---------------|
| Order number | 251912 32/08 |
| GTIN | 4045197656957 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-----------------|
| Shank size | 32 mm |
| Functional width L ₄ | 40 mm |
| Pin | 259049 2 |
| Shim | 259031 41 |
| ISO code toolholder | MWLNR/L 3232P08 |
| Clamping claw | 259038 12 |
| Insert size | 8 mm |
| suitable indexable insert | WN.. 0804.. |
| Head length L ₁ | 32 mm |
| Screw set | 259023 2 |
| Overall length L | 170 mm |
| Standard | Works standard |
| Application type | right-hand |
| Through-coolant | no |
| Setting angle κ | 95 degrees |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|------------|
| Set of screws 10 pieces Type 2 | 259023 2 |
| Shim Type 41 | 259031 41 |
| Clamping claw Type 12 | 259038 12 |
| Pin Type 2 | 259049 2 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm | 674242 3 |