

Garant

Carbide boring bar E.. SCLCR 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 4/03mm


Order data

Order number	260016 4/03
GTIN	4045197651778
Item class	21T

Technical description

Insert size	3 mm
ISO code toolholder	E04G SCLCR/L03
suitable indexable insert	CC.. 0301..
Minimum pre-drill Ø D_{min}	5 mm
Pack of insert screws	269028 13
Centre offset L_3	2.5 mm
Head length L_1	10 mm
Overall length L	90 mm
Clamping height L_2	3.8 mm
Setting angle κ	95 degrees
Shank Ø D_s	4 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 13	269028 13
Set of insert screws Type 6	269028 6
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6