

Garant

Carbide boring bar E.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 6/03mm


Order data

Order number	260017 6/03
GTIN	4045197651877
Item class	21T

Technical description

Minimum pre-drill Ø D_{min}	7 mm
suitable indexable insert	CC.. 0301..
Centre offset L_3	3.5 mm
Head length L_1	10 mm
Insert size	3 mm
Pack of insert screws	269028 19
ISO code toolholder	E06J SCLCR/L03
Overall length L	110 mm
Clamping height L_2	5.8 mm
Setting angle κ	95 degrees
Shank Ø D_s	6 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 19	269028 19
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6