

Garant

Steel boring bar A.. MWLNR 95°, for indexable inserts WN.., right-hand, Shank Ø / insert size: 32/08mm


Order data

Order number	251936 32/08
GTIN	4045197651426
Item class	21T

Technical description

Pin	259049 5
ISO code toolholder	A32S MWLNR/L08
Minimum pre-drill Ø D_{min}	40 mm
Centre offset L_3	22 mm
Clamping claw	259038 12
suitable indexable insert	WN.. 0804..
Insert size	8 mm
Shim	259031 41
Screw set	259023 3
Overall length L	250 mm
Clamping height L_2	31 mm
Setting angle κ	95 degrees
Shank Ø D_s	32 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of screws 10 pieces Type 3	259023 3
Shim Type 41	259031 41
Clamping claw Type 12	259038 12
Pin Type 5	259049 5
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15