

Garant

Carbide boring bar E.. SCLCR 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 5/03mm


Order data

Order number	260016 5/03
GTIN	4045197651785
Item class	21T

Technical description

suitable indexable insert	CC.. 0301..
Minimum pre-drill Ø D_{min}	6 mm
Insert size	3 mm
ISO code toolholder	E05H SCLCR/L03
Centre offset L_3	3 mm
Head length L_1	10 mm
Pack of insert screws	269028 19
Overall length L	100 mm
Clamping height L_2	4.8 mm
Setting angle κ	95 degrees
Shank Ø D_s	5 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 19	269028 19
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6