

Garant

Carbide boring bar E.. SCLCL 95°, for indexable inserts CC.., left-hand, Shank Ø / insert size: 8/06mm


Order data

Order number	260017 8/06
GTIN	4045197651884
Item class	21T

Technical description

Insert size	6 mm
suitable indexable insert	CC.. 0602..
Pack of insert screws	269028 7
Minimum pre-drill Ø D_{min}	10 mm
ISO code toolholder	E08K SCLCR/L06
Head length L_1	10 mm
Centre offset L_3	5 mm
Overall length L	125 mm
Clamping height L_2	7.6 mm
Setting angle κ	95 degrees
Shank Ø D_s	8 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8