

Garant
Clamping toolholder, left-hand, Shank / insert size: 25/08mm

Order data

Order number	251913 25/08
GTIN	4045197651280
Item class	21T

Description

Clamping toolholder 25/08 mm ISO code toolholder: MWLNR/L 2525M08
 suitable indexable insert: WN.. 0804..
 Functional width L_4 : 32 mm
 Head length L_1 : 31 mm
 Overall length L: 150 mm
 Screw set: 259023 2

Technical description

Shank size	25 mm
Clamping claw	259038 12
suitable indexable insert	WN.. 0804..
Head length L_1	31 mm
ISO code toolholder	MWLNR/L 2525M08
Pin	259049 2
Functional width L_4	32 mm
Screw set	259023 2
Insert size	8 mm
Shim	259031 41
Overall length L	150 mm

Series	QuickTurn
Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	95°
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Pin	259600
Shim	259580
Clamping claw	259560
Set of screws 10 pieces Type 2	259023 2
Set of screws 10 pieces	259620
Clamping claw Type 12	259038 12
Shim Type 41	259031 41
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Pin Type 2	259049 2