

Garant

Carbide boring bar E.. SCLCR 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 12/06mm


Order data

Order number	260016 12/06
GTIN	4045197651822
Item class	21T

Technical description

Pack of insert screws	269028 7
Insert size	6 mm
suitable indexable insert	CC.. 0602..
Centre offset L_3	8 mm
ISO code toolholder	E12M SCLCR/L06
Minimum pre-drill Ø D_{min}	14 mm
Head length L_1	10 mm
Overall length L	150 mm
Clamping height L_2	11.5 mm
Setting angle κ	95 degrees
Shank Ø D_s	12 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8