

**Garant**
**Carbide boring bar E.. SCLCR, for indexable inserts CC., right-hand**

**Order data**

Order number	260018
GTIN	4045197651938
Item class	29W

**Technical description**

ISO code toolholder	E10K SCLCR/L06
ISO code toolholder	E08K SCLCR/L06
ISO code toolholder	E12M SCLCR/L06
Pack of insert screws	269028 7
suitable indexable insert	CC.. 0602..
Centre offset $L_3$	5 mm
Centre offset $L_3$	6 mm
Centre offset $L_3$	8 mm
Minimum pre-drill $\varnothing D_{\min}$	10 mm
Minimum pre-drill $\varnothing D_{\min}$	12 mm
Minimum pre-drill $\varnothing D_{\min}$	14 mm
Clamping height $L_2$	7.6 mm
Clamping height $L_2$	9.6 mm
Clamping height $L_2$	11.5 mm

Overall length L	125 mm
Overall length L	125 mm
Overall length L	150 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes
Type of product	Boring bar

---

## Accessories

Boring bar carbide Shank Ø / insert size 10/06 mm	260016 10/06
Boring bar carbide Shank Ø / insert size 12/06 mm	260016 12/06
Boring bar carbide Shank Ø / insert size 8/06 mm	260016 8/06
Set of insert screws Type 7	269028 7