

Garant
**Clamping toolholder PSKNR 75°, for indexable inserts SN., right-hand,
Shank / insert size: 25/15mm**

Order data

Order number	251110 25/15
GTIN	4045197650818
Item class	21T

Technical description

Insert size	15 mm
Shim	259031 37
suitable indexable insert	SN.. 1506..
Shank size	25 mm
Shim punches pack	259047 4
Shim pins pack	259044 6
Lever screw	259018 11
Head length L ₁	30 mm
Functional width L ₄	32 mm
Lever	259015 12
ISO code toolholder	PSKNR/L 2525M15
Overall length L	150 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 37	259031 37
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15