

**Garant**

**Carbide boring bar E.. SCLCR 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 16/09mm**


**Order data**

|              |               |
|--------------|---------------|
| Order number | 260016 16/09  |
| GTIN         | 4045197651839 |
| Item class   | 21T           |

**Technical description**

|   |                |
|---|----------------|
| Pack of insert screws                   | 269028 8       |
| suitable indexable insert               | CC.. 09T3..    |
| Centre offset $L_3$                     | 10 mm          |
| ISO code toolholder                     | E16R SCLCR/L09 |
| Head length $L_1$                       | 16 mm          |
| Insert size                             | 9 mm           |
| Minimum pre-drill $\varnothing D_{min}$ | 18 mm          |
| Overall length L                        | 200 mm         |
| Clamping height $L_2$                   | 15.5 mm        |
| Setting angle $\kappa$                  | 95 degrees     |
| Shank $\varnothing D_s$                 | 16 mm          |
| Standard                                | DIN 8024       |
| Application type                        | right-hand     |
| Boring depth up to                      | 8×D            |
| Tool material                           | Carbide        |
| Through-coolant                         | yes            |

|                 |                               |
|-----------------|-------------------------------|
| Application     | Internal longitudinal turning |
| Type of product | Boring Bar                    |

---

## Accessories

|  |             |
|--|-------------|
| Set of insert screws Type 8  | 269028 8    |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500  |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15                            | 674248 TX15 |