

Garant

Clamping toolholder SDJCL 93°, for indexable inserts DC., left-hand, Shank / insert size: 12/07mm



Order data

Order number	260309 12/07
GTIN	4045197652614
Item class	21T

Technical description

Shank size	12 mm
Insert size	7 mm
Pack of insert screws	269028 22
Functional width L ₄	16 mm
suitable indexable insert	DC.. 0702..
Head length L ₁	17 mm
ISO code toolholder	SDJCR/L 1212F07
Overall length L	80 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15