

**Garant**
**Carbide boring bar E.. SCLCL, for indexable inserts CC.., left-hand**

**Order data**

Order number	260019
GTIN	4045197651945
Item class	29W

**Technical description**

Pack of insert screws	269028 7
suitable indexable insert	CC.. 0602..
ISO code toolholder	E08K SCLCR/L06
ISO code toolholder	E10K SCLCR/L06
ISO code toolholder	E12M SCLCR/L06
Clamping height L <sub>2</sub>	7.6 mm
Clamping height L <sub>2</sub>	9.6 mm
Clamping height L <sub>2</sub>	11.5 mm
Minimum pre-drill $\varnothing D_{\min}$	10 mm
Minimum pre-drill $\varnothing D_{\min}$	12 mm
Minimum pre-drill $\varnothing D_{\min}$	14 mm
Centre offset L <sub>3</sub>	5 mm
Centre offset L <sub>3</sub>	6 mm
Centre offset L <sub>3</sub>	8 mm

Overall length L	125 mm
Overall length L	125 mm
Overall length L	150 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes
Type of product	Boring bar

---

## Accessories

Boring bar carbide Shank Ø / insert size 10/06 mm	260017 10/06
Boring bar carbide Shank Ø / insert size 12/06 mm	260017 12/06
Boring bar carbide Shank Ø / insert size 8/06 mm	260017 8/06
Set of insert screws Type 7	269028 7