

Garant
**Clamping toolholder SDHCR 107,5°, for indexable inserts DC., right-hand,
Shank / insert size: 12/07mm**

Order data

Order number	260306 12/07
GTIN	4045197654878
Item class	21T

Technical description

suitable indexable insert	DC.. 0702..
Insert size	7 mm
Functional width L ₄	16 mm
Shank size	12 mm
Head length L ₁	12 mm
ISO code toolholder	SDHCR/L 1212F07
Pack of insert screws	269028 22
Overall length L	80 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15