

**Garant****Clamping toolholder PSKNL 75°, for indexable inserts SN., left-hand, Shank / insert size: 25/15mm****Order data**

Order number	251111 25/15
GTIN	4045197656766
Item class	21T

**Technical description**

Shim	259031 37
Lever	259015 12
Shim pins pack	259044 6
Shim punches pack	259047 4
Head length L <sub>1</sub>	30 mm
ISO code toolholder	PSKNR/L 2525M15
Shank size	25 mm
suitable indexable insert	SN.. 1506..
Functional width L <sub>4</sub>	32 mm
Insert size	15 mm
Lever screw	259018 11
Overall length L	150 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 37	259031 37
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15