

Garant

Clamping toolholder PSSNL 45°, for indexable inserts SN., left-hand, Shank / insert size: 32/15mm



Order data

Order number	251113 32/15
GTIN	4045197656902
Item class	21T

Technical description

Functional width L ₄	40 mm
ISO code toolholder	PSSNR/L 3232P15
Shank size	32 mm
Shim	259031 37
Insert size	15 mm
Head length L ₁	36 mm
Lever	259015 12
suitable indexable insert	SN.. 1506..
Lever screw	259018 11
Shim punches pack	259047 4
Shim pins pack	259044 6
Overall length L	170 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 37	259031 37
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15