

**Garant**

**Clamping toolholder SDJCR 93°, for indexable inserts DC., right-hand,  
Shank / insert size: 12/07mm**



## Order data

Order number	260308 12/07
GTIN	4045197652577
Item class	21T

## Technical description

Insert size	7 mm
Pack of insert screws	269028 22
Head length L <sub>1</sub>	17 mm
Functional width L <sub>4</sub>	16 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	SDJCR/L 1212F07
Shank size	12 mm
Overall length L	80 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15