

Garant

Steel boring bar A.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 10/06mm


Order data

Order number	260033 10/06
GTIN	4045197652317
Item class	21T

Technical description

ISO code toolholder	A10K SCLCR/L06
suitable indexable insert	CC.. 0602..
Centre offset L_3	7 mm
Pack of insert screws	269028 22
Insert size	6 mm
Minimum pre-drill $\varnothing D_{min}$	12 mm
Overall length L	125 mm
Clamping height L_2	9 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	10 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8