

Garant

Steel boring bar A.. SCLCL 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 8/06mm


Order data

Order number	260032 8/06
GTIN	4045197652225
Item class	21T

Technical description

ISO code toolholder	A08H SCLCR/L06
Pack of insert screws	269028 7
Insert size	6 mm
Centre offset L_3	6 mm
suitable indexable insert	CC.. 0602..
Minimum pre-drill $\varnothing D_{min}$	10 mm
Overall length L	100 mm
Clamping height L_2	7 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	8 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8