

Garant

**Carbide boring bar E.. SDUCR 93°, for indexable inserts DC., right-hand,
Shank Ø / insert size: 12/07mm**


Order data

Order number	260318 12/07
GTIN	4045197652676
Item class	21T

Technical description

suitable indexable insert	DC.. 0702..
Insert size	7 mm
Centre offset L_3	9 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	15 mm
ISO code toolholder	E12M SDUCR/L07
Overall length L	150 mm
Clamping height L_2	11.6 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	12 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8