

Garant

**Carbide boring bar E.. SDUCR 93°, for indexable inserts DC.., right-hand,
Shank Ø / insert size: 16/07mm**


Order data

Order number	260318 16/07
GTIN	4045197652683
Item class	21T

Technical description

ISO code toolholder	E16R SDUCR/L07
Pack of insert screws	269028 7
Minimum pre-drill Ø D _{min}	19 mm
Centre offset L ₃	11 mm
suitable indexable insert	DC.. 0702..
Insert size	7 mm
Overall length L	200 mm
Clamping height L ₂	15.6 mm
Setting angle κ	93 degrees
Shank Ø D _s	16 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8