

Garant

Carbide boring bar E.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 10/07mm


Order data

Order number	260319 10/07
GTIN	4045197652713
Item class	21T

Technical description

ISO code toolholder	E10K SDUCR/L07
Centre offset L_3	7 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
Insert size	7 mm
suitable indexable insert	DC.. 0702..
Overall length L	125 mm
Clamping height L_2	9.6 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8