

**Garant**

**Carbide boring bar E.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 16/07mm**


**Order data**

Order number	260319 16/07
GTIN	4045197652737
Item class	21T

**Technical description**

Minimum pre-drill Ø $D_{min}$	19 mm
suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 7
ISO code toolholder	E16R SDUCR/L07
Insert size	7 mm
Centre offset $L_3$	11 mm
Overall length L	200 mm
Clamping height $L_2$	15.6 mm
Setting angle $\kappa$	93 degrees
Shank Ø $D_s$	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

---

## Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8