

**Garant**

**Carbide boring bar E.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 20/11mm**


**Order data**

Order number	260319 20/11
GTIN	4045197652744
Item class	21T

**Technical description**

ISO code toolholder	E20S SDUCR/L11
Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
Insert size	11 mm
Centre offset $L_3$	13.1 mm
Minimum pre-drill $\varnothing D_{\min}$	23.5 mm
Overall length L	250 mm
Clamping height $L_2$	18.9 mm
Setting angle $\kappa$	93 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

---

## Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15