

Garant
Clamping toolholder PDJNL 93°, for indexable inserts DN., left-hand, Shank / insert size: 32/15mm

Order data

Order number	250611 32/15
GTIN	4045197654625
Item class	21T

Technical description

Shim pins pack	259044 2
suitable indexable insert	DN.. 1506..
Shim	259031 28
Lever screw	259018 7
Lever	259015 8
Head length L ₁	36 mm
Shank size	32 mm
Insert size	15 mm
ISO code toolholder	PDJNR/L 3232P15
Functional width L ₄	40 mm
Shim punches pack	259047 2
Overall length L	170 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 8	259015 8
Lever screw Type 7	259018 7
Shim Type 28	259031 28
Set of shim pins 10 pieces Type 2	259044 2
Shim punches set 10 pieces Type 2	259047 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3