

Garant
Shrink-fit chuck, SK 40 A = 200, Clamping range \varnothing D1: 20mm

Order data

Order number	302278 20
GTIN	4045197294500
Item class	31A

Description
Version:

- **High-temperature steel.**
- **Size 3 -5 for carbide, from size 6 for HSS and carbide.**
- **All shanks hard turned (for smooth running!).**
- **With RFID / Balluffchip bore.**

Application:

For clamping tools with parallel shank to h6 tolerance.
Suitable for inductive, contact, and hot-air shrink units.

Optional extras:

Pull studs (PS) No. 308600 – 308800. PS wrenches No. 308820 – 308835, Shrink-fit chuck extensions No. 302410 – 302419. Shrink-fit units, accessories No. 354210 – 354450, balancing screws set No. 309906 size 180.

Technical description

\varnothing D ₂	33 mm
Overhang dimension A	200 mm
Clamping \varnothing D ₁	20 mm
External \varnothing D	42 mm
Adapter	SK 40 A = 200
Arbor standard	ISO 7388-1
Shape	ADB

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

Accessories

Screening plate for coilSU1 for clamping Ø 12-20 mm	354240 12-20
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Screening plate for coilSU1 for clamping Ø 20-32 mm	354240 20-32
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Shrink-fit unit Type SU1	354210 SU1
Pull studsealed, form B suitable for steep tapers 40	308620 40
Shrink-fit chuck extension 4.5°with length adjustment screw Ø d / Ø D1 32/20 mm	302412 32/20
Cooling unit Type CU1	354215 CU1
Pull studForm A suitable for steep tapers 40	308600 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
	302410 32/20

Shrink-fit chuck extension 4.5° without length adjustment
screw Ø d / Ø D1 32/20 mm

Pull stud Form B suitable for steep tapers 40	308640 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Basic tool mounting for SK for SK taper shank 40	354225 40
Pull stud sealed, form A suitable for steep tapers 40	308610 40
Pull stud sealed suitable for steep tapers 40	308660 40
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 32/20 mm	302416 32/20
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40	308605 40
Cooling adapter short 4.5° for clamping Ø 16,1-22 mm	354235 16,1-22
Pull stud Mazak, form A suitable for steep tapers 40M	308670 40M
Pull stud sealed suitable for steep tapers 40	308635 40
Cooling adapter long 4.5° for clamping Ø 16,1-22 mm	354236 16,1-22
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40